

M- stitch THE PERFECT MATCH!

PEGASUS offers stable quality with the "seam opener device" and the reliable "MXneo" that can reduce the burden of manual work.



MXneo



Seam Opener
Device



MX5203-A-02/223-4/Y2261





PEGASUS CO., LTD.

5-7-2 Sagisu Fukushima-ku, Osaka 553-0002 Japan
TEL : +81-6-6458-4739 FAX : +81-6-6454-8785

Specifications and appearance are subjected to changes without notice.
Read the instruction manual before operating the machine to ensure safe usage.
Photos for illustration purpose. They may not represent actual operating conditions and/or displayed optional parts.



Use as a set to increase efficiency



MX5203-A-02/223-4/Y2261

Application	Fabric weight	Subclass	No.of needles	No.of threads	Overedge width (mm)	Stitch length (mm)	Diff.feed ratio	Presser foot lift (mm)	Max.speed (sti/min)	Needles
M-stitch	Light to Medium	MX5203-A-02 223-4/Y2261	1	2	4	0.6-3.8	0.7-2.0	5	8,000	Organ DC-27 #9



The process of opening the fabric evenly after sewing can be completed quickly and evenly.



Opening by hand takes too much time, stretches the fabrics and results in uneven quality.

